Product datasheet

Specifications





APC Smart-UPS On-Line, 5kVA, Tower, 230V, 6x C13+4x C19, NMC, Preventive Maint, EcoStruxure IT Expert, W/O rail kit

SRT5KXLI-PMITE

Overview

Lead Time Usually in Stock

Main

IVIAIII	
Main Input Voltage	230 V
Other Input Voltage	220 V
Main Output Voltage	230 V
Other Output Voltage	220 V
Rated Power In W	4500 W
Rated Power In Va	5000 VA
Output Connection Type	6 IEC 60320 C13
Provided Equipment	CD with software

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	2
Number Of Battery Free Slots	0
Battery Recharge Time	1.5 h
Number Of Battery Replacement Quantity	1
Battery Voltage	192 V
Battery Charger Power	560 W rated
Battery Life	35 year(s)
Extended Runtime	1

General

Ups Type	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No



Physical

Colour	Black
Height	43.2 cm
Width	13 cm
Depth	71.94 cm
Net Weight	54.43 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit
Two Post Mountable	0
Usb Compatible	Yes

Input

Network Frequency	4070 Hz auto-sensing
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E)
Input Voltage Limits	100275 V adjustable (half load)

Output

Maximum Configurable Power In Va	5000 VA
Maximum Configurable Power In W	4500 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3:1
Bypass Type	Internal bypass (automatic and manual)

Conformance

Product Certifications	CE
Marking	CE Mark

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1545 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	55 dBA
Heat Dissipation	931 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1	
Preinstalled Device	Network management card 3 with environmental monitoring	
Alarm	Audible and visible alarms : prioritized by severity	
Emergency Power Off	Yes	

Surge Protection and Filtering

Surge Energy Rate 480 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33 cm
Package 1 Width	96 cm
Package 1 Length	61 cm
Package 1 Weight	63.9 kg

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information