

# Product datasheet

Specifications



## Rack ATS, 200/208V, 30A, L6-30 in, (16) C13 (2) C19 out

AP4432

⚠ To be discontinued on: 30 December 2022

⚠ To be discontinued

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	200 V 208 V
Main Output Voltage	200 V 208 V
Plug standard	NEMA L6-30P
Number of rack unit	2U
Cable length	2.44 m
Number of cables	2
Provided equipment	Mounting hardware Rack mounting brackets RS-232 configuration cable

### Physical

Height	8.8 cm
Width	43.2 cm
Depth	23.6 cm
Net weight	6.58 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

### Input

Network frequency	50/60 Hz
[In] rated current	24 A
Max line current	30 A
Input current limits	30 A
Load capacity	4992 VA

## Output

Max current draw	30 A
Number of power socket outlets	16 IEC 60320 C13 2 IEC 60320 C19
Protection type	Circuit breaker

## Conformance

Product certifications	PSE TÜV-C TÜV-NURTL
Standards	EN 55022 class A FCC part 15 class A

## Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	9.07 kg
Package 1 Height	21 cm
Package 1 width	58.4 cm
Package 1 Length	35.6 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------