Product datasheet

Specifications





APC 17" Rack LCD Console -United Kingdom

AP5717UK

Overview

Lead Time	Usually in Stock
Main	
Main Input Voltage	100 V 240 V
Number Of Rack Unit	1U
Provided Equipment	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Single user rack mount kit USB cable USB KVM cable

Physical

Colour	Black
Height	4.4 cm
Width	48.2 cm
Depth	61.4 cm
Net Weight	15.9 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	104.98 cm
Minimum Mounting Depth	68 cm

Input

Network Frequency

50/60 Hz

Conformance

Product Certifications

C-Tick GOST Industry Canada NOM UL listed VDE



Standards

EN 55022 class A EN 55024 EN 60950 FCC part 15 class A IEC 60950

Environmental

Supported Hardware

Display Colour	16 colours
Display Size	17 inch
Trackball Type	PS/2 touchpad USB mouse
Display Type	LCD display
Display Power Consumption	19 W
Pixel Size	0.26

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	82.6 cm
Package 1 Length	67.3 cm
Package 1 Weight	19.46 kg

Contractual warranty


Warranty

2 years repair or replace



Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

