



# Power Cord Kit (6 EA), Locking, C19 TO C20, 0.6M (2FT), Red

AP8712SX340

#### Overview

Lead Time Usually in Stock

#### Main

Input Connection Type	IEC 60320 C20
Cable Length	0.61 m
Number Of Cables	6

## **Physical**

Colour	Red
Height	30 cm
Width	6 cm
Depth	6.5 cm
Net Weight	1.12 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

### Input

Max Line Current	16 A
Input Current Limits	16 A

# Output

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Power Cable Length	0.61 m

#### **Conformance**

Product Certifications	CCC
	CSA
	PSE
	UL listed
	VDF

#### **Environmental**

Ambient Air Temperature For Operation	075 °C
Relative Humidity	2080 %

Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.00 15240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	6.5 cm
Package 1 Length	6 cm
Package 1 Weight	1.12 kg

# **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

#### Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Lead Free

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant
EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information