
# **Product datasheet**

Specifications





## **Overview**

Lead Time	Usually in Stock
Main	
Product Or Component Type	UPS network management cards
Provided Equipment	User manual USB cable
Physical	
Height	3.8 cm
Width	12.1 cm
Depth	11.4 cm
Net Weight	0.08 kg

Net Weight	0.08 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

## Conformance

Standards	EN 55022 class A EN 55024 ICES-003
Product Certifications	AS/NZS 3548 (C-Tick) class A FCC part 15 class A GOST VCCI class A

## Environmental

Ambient Air Temperature For Operation	045 °C
Operating Altitude	010000 ft
Relative Humidity	095 %
Ambient Air Temperature For Storage	-545 °C
Storage Altitude	0.0015240.00 m
Storage Relative Humidity	095 %

## **Communications & Management**

Authentication

Radius

# **Packing Units**



Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	15.9 cm
Package 1 Length	23.5 cm
Package 1 Weight	0.34 kg

## **Contractual warranty**

Warranty

2 years repair or replace

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



#### **Resource performance**

Energy Efficient Product

Take-Back Program Available

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile



