


# APC Back-UPS™ 600

Part Number: BX600L-LM



## Battery Backup Protection for Computers and Electronics

The Back-UPS 600 from APC by Schneider Electric protects your computer and electronic equipment from destructive power outages by providing short term battery power during an outage. The Back-UPS 600 features Automatic Voltage Regulation (AVR), which instantly adjusts high and low voltage fluctuations to safe levels for your electronics, saving battery power for when you need it most during storms and power outages. Equipped with NEMA 5-15R sockets, the BX600L-LM keeps your desktop computer, monitor or other critical devices (router, modem, television, etc.) running when the power goes out. Specifically designed to protect electronic equipment in harsh power environments, the Back-UPS 600 ensures maximum productivity and work efficiency.



## Product Features

- 1 LED Indicator and Audible Alarms  
Quickly understand the unit and power status through visual and audible indicators.
- 2 Automatic Voltage Regulation (AVR)  
“Boost and Trim” AVR instantly corrects voltage fluctuations without using the battery, allowing you to work indefinitely through inconsistent power, saving battery life for power outages.
- 3 4 Battery Backup and Surge Protected Sockets  
Keep critical electronic equipment running when the power goes out, so you can protect your work and save your data.
- 4 Replaceable Fuse Circuit Breaker  
Provides for easy recovery from circuit overloads and protects your UPS and connected electronics from electrical damage.
- 5 Automatic Diagnostic Testing  
Periodic battery self-test ensures early detection of a battery that needs to be replaced, ensuring your unit is ready when you need it.
- 6 2 Yr Warranty  
APC offers a 2 year warranty on the UPS and 1 year warranty on the battery with free technical phone and online support, providing customer peace of mind.
- 7 Easy to use “one step” battery connector.



**APC**  
by Schneider Electric

## Back-UPS BX600L-LM Specifications

Model Number	BX600L-LM
<b>Output</b>	
Output Capacity	600VA / 300Watts
Output Voltage / Frequency (On utility)	120V , 55-65Hz+/-1Hz
Output Voltage / Frequency (On battery)	120V, 60 Hz +/-1 Hz
Output Connections	4 NEMA 5-15R sockets (all with battery backup protection)
Waveform Type	Stepped Approximation to Sine Wave
<b>Input</b>	
Input Voltage / Frequency	89-145V, 55-65Hz+/-1Hz
Input Connection	NEMA Input Power cord
<b>Physical</b>	
Unit Dimensions (H x W x D)	142 x 101 x 300 mm
Unit Weight	4.4kg
Shipping Dimensions (H x W x D)	223 x 143 x 347 mm
Shipping Weight	4.6kg
Color	Black
UPC Code	731304323181
<b>Battery</b>	
Battery Type	Maintenance-free, sealed lead-acid battery, leak proof
Battery Size	12 volt, 7 Ah
<b>Management</b>	
Alarms	Visual (LED) and audible alarms
<b>Conformance</b>	
Warranty	2 years repair or replace (excluding battery) and 1 year for battery
Regulatory Approvals	cTUVus , FCC Class A

**APC by Schneider Electric**

132 Fairgrounds Rd  
West Kingston, RI 02892

www.apc.com

**APC**<sup>®</sup>  
by Schneider Electric