## **Product datasheet**

Specifications





# APC Performance SurgeArrest 8 outlets 230V UK

PM8-UK

! To be discontinued on: 30 Apr 2024

(!) To be discontinued

#### **Overview**

Lead Time Usually in Stock

#### Main

Main Input Voltage	230 V
Input Connection Type	BS1363A British
Cable Length	2.00 m
Number Of Cables	1
Provided Equipment	User manual

#### **Physical**

Colour	White
Height	6.17 cm
Width	32.65 cm
Depth	11.03 cm
Net Weight	0.91 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

#### Input

Network Frequency	50 Hz +/- 5 Hz
Maximum Input Current	13 A
Switching Current Capacity	13 A

#### **Output**

Number Of Power Socket Outlets	8
Outlet Standard	BS 1363 United Kingdom

#### **Conformance**

Product Certifications	CE
Equipment Protection Policy	Lifetime : 50000 euros

#### **Environmental**



Ambient Air Temperature For Operation	040 °C
Relative Humidity	090 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-540 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.004572.00 m

## **Surge Protection and Filtering**

Common Mode Rejection	60 dB
Peak Current	48 kAcommon mode 60 kAnormal mode
Surge Energy Rate	2754 J

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	36.5 cm
Package 1 Width	6.4 cm
Package 1 Length	17 cm
Package 1 Weight	1.05 kg
Scc14	10731304313592

## **Contractual warranty**

Warranty Limited Lifetime (European Union countries only)



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >





Transparency RoHS/REACh

#### Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information