# **Product datasheet**

Specifications



# Rack ATS, 200/208V, 30A, L6-30 in, (16) C13 (2) C19 out



AP4432

! Discontinued on: Jun 9, 2023



#### **Overview**

Lead Time Usually in Stock

## Main

Main		
Main Input Voltage	200 V 208 V	
Main Output Voltage	200 V 208 V	
Input Connection Type	NEMA L6-30P	
Number Of Rack Unit	2U	
Cable Length	2.44 m	
Number Of Cables	2	
Provided Equipment	Mounting hardware Rack mounting brackets RS-232 configuration cable	

## **Physical**

Height	8.8 cm
Width	43.2 cm
Depth	23.6 cm
Net Weight	6.58 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Rack-mounted

## Input

Network Frequency	50/60 Hz
[In] Rated Current	24 A
Max Line Current	30 A
Input Current Limits	30 A
Load Capacity	4992 VA

## **Output**

Max Current Draw 30 A

Number Of Power Socket Outlets	16 IEC 60320 C13 2 IEC 60320 C19
Protection Type	Circuit breaker

## Conformance

Product Certifications	PSE TÜV-C TÜV-NURTL
Standards	EN 55022 class A FCC part 15 class A

## **Environmental**

Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21 cm
Package 1 Width	35.6 cm
Package 1 Length	58.4 cm
Package 1 Weight	9.07 kg

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

### Resource performance



Take-Back Program Available

## Well-being performance



Lead Free



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information