# **Product datasheet**

Specifications





# APC Replacement Battery Cartridge, VRLA battery, 7Ah, 12VDC, 2-year warranty

APCRBC110

#### Overview

Lead Time

Usually in Stock

#### Main

| Product Or Component Type | Replacement battery cartridge  |
|---------------------------|--|
| Battery Type              | Lead-acid battery  |
| Provided Equipment        | All required connectors<br>Battery recycling guide<br>Reusable packaging<br>Installation guide |

## **Batteries & Runtime**

| Number Of Battery Filled Slots | 0                        |
|--------------------------------|--------------------------|
| Device Mounting                | Enclosed battery cabinet |
| Battery Voltage                | 12 V                     |
| Number Of Battery Replacement  | 1                        |

Number Of Battery Replacement Quantity

## Physical

| Colour         | Black              |
|----------------|--------------------|
| Height         | 10.5 cm            |
| Width          | 15.1 cm            |
| Depth          | 6.5 cm             |
| Net Weight     | 2.5 kg             |
| Mounting Mode  | Not rack-mountable |
| Usb Compatible | No                 |

## Output

Battery Capacity

7.0 Ah

### Environmental

| Ambient Air Temperature For<br>Operation | 040 °C         |
|--|----------------|
| Operating Altitude                       | 010000 ft      |
| Relative Humidity                        | 095 %          |
| Ambient Air Temperature For<br>Storage   | -1545 °C       |
| Storage Altitude                         | 0.0015240.00 m |



Storage Relative Humidity 0...95 %

## **Packing Units**

| · acting child               |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 8.4 cm  |
| Package 1 Width              | 17.5 cm |
| Package 1 Length             | 21 cm   |
| Package 1 Weight             | 2.36 kg |

# **Contractual warranty**

Warranty

2 years repair or replace

# Sustainability

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.





Take-back Transparency RoHS/REACh

#### **Resource performance**

Take-Back Program Available

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |

