# **Product datasheet**

Specifications





# In-Line Current Meter, 16A, 230V, IEC309-16A, 2P+G

AP7152B

#### Overview

Lead Time Usually in Stock

## Main

Colour	Black	
Cord Length	0.91 m	
Number Of Cables	1	
Provided Equipment	Documentation CD Rack mounting brackets RS-232 configuration cable	

## Complementary

Input Voltage	200 V 208 V 230 V
Height	4.4 cm
Width	17.8 cm
Output Voltage	230 V
Depth	14 cm
Net Weight	1.84 kg
Mounting Location	Тор
Mounting Preference	No preference
Input Plug Type	IEC 60309 16 A 2P + E
Mounting Mode	Rack-mounted
Rack Units	OU
Mounting Position	Vertical
Permissible Voltage	220250 V
Max Line Current	16 A
Input Current Limits	16 A
Load Capacity	3680 VA
Number Of Power Socket Outlets	1
Network Frequency	50/60 Hz
Total Number Of Outlets	1 IEC 60309 16 A 2P + E

## **Environment**



Product Certifications	AS/NZS 3548 (C-Tick) class A
	C-Tick
	CE
	GOST
	VDE
Standards	EN 55022 class A
	EN 55024
	EN 61000-3-2
	EN 61000-3-3
	IEC 61000-3-2
	IEC 61000-3-3
Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.6 cm
Package 1 Width	18.5 cm
Package 1 Length	33 cm
Package 1 Weight	2.48 kg

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

## Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Lead Free

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information