


Scale Reference Architectures



Purpose-built and pre-validated solutions for Scale Enterprise platform and Scale platform for SMB and Remote Office/Branch Office space.

APC by Schneider Electric provides a purpose-built infrastructure and physical management wrapper for Scale hyperconverged architectures, allowing organizations to simply and efficiently deliver a complete and highly energy-efficient IT solution that is pre-tested, optimized, and able to be rapidly deployed. This creates a reliable and robust environment to leverage the best of on-premises and multi-cloud infrastructures.

Enterprise Reference Architecture




| Enterprise Solutions | | |
|----------------------|---|--|
| Scale HC4100 | 4 | HC4100 HC4150 Series |
| Switch | | Mellanox SX1012 48 port 10 Gbe |
| Rack | 1 | AR3100SP NetShelter SX 42U with Shock Pallet |
| UPS | 2 | SRT5KRMXLT Smart UPS 5000VA RM 208V |
| rPDU | 2 | AP8941 Rack PDU, Switched Zero U, 30A, 200/208V,(21) C13 & (3) C19 |
| Power Cord Kit | 1 | AR8706S-NA Power Cord Kit (6 ea), Locking, C13 to C14, 1.8m, North America |
| NetBotz 250 | 1 | NBACS125 NetBotz 125kHz Rack Access Control |
| Cable Management | 1 | AR8429 Horizontal Cable Organizer 1U w/brush strip |
| Options | | |
| Software | | EcoStruxure IT Advisor |
| Services | | Lifecycle Services |
| Office Rack Solution | | NetShelter CX Product Family |

Schneider Electric provides an infrastructure and physical management wrapper around converged and hyperconverged infrastructures. This added 'wrapper' completes the product to enable organizations to simply and efficiently deliver a complete and highly energy efficient IT solution that is pre-tested, optimized and able to be rapidly deployed across an organization.

Schneider Electric's management tools allow for remote management that seamlessly integrate with the IT hardware, reducing the need and cost of onsite IT support staff.

Remote Office/Branch Office and SMB Reference Architecture



| Remote Office/Branch Office and SMB locations | | |
|---|---|--|
| Scale HC1000 | 2 | HC1000, HC1150, HC1150D, HC1150DF |
| Rack | 1 | AR3104SP1 NetShelter SX 24U with Shock Pallet |
| Switch | | Mellanox SX1012 48 port 10 Gbe |
| UPS | 2 | SMX3000RMLV2UNC Smart UPS X 3000VA Rack/Tower LCD 100-127V with Network Card |
| rPDU | 2 | AP7902B Rack PDU, Switched 2U, 30A, 120V, (16)5-20 |
| Power Cord Kit | 1 | AR8706S-NA Power Cord Kit (6 ea.), Locking, C13 to C14, 1.8m, North America |
| NetBotz 250 | 1 | NBACS125 NetBotz 125kHz Rack Access Control |
| Cable Management | 1 | AR8429 Horizontal Cable Organizer 1U w/brush strip |
| Power Cord Kit | 1 | AP9891 Power Cord Kit (5 ea.), C13 to 5-15P, 0.6m |
| Blanking panels | 1 | AR8136BLK Toolless Airflow Management Blanking Panel - Qty 10 |
| Options | | |
| Software | | EcoStruxure IT Expert |
| Services | | Lifecycle Services |
| Office Rack Solution | | NetShelter CX Product Family |

Schneider Electric provides an infrastructure and physical management wrapper around converged and hyperconverged infrastructures. This added 'wrapper' completes the product to enable organizations to simply and efficiently deliver a complete and highly energy efficient IT solution that is pre-tested, optimized and able to be rapidly deployed across an organization.

Schneider Electric's management tools allow for remote management that seamlessly integrate with the IT hardware, reducing the need and cost of onsite IT support staff.