

Product datasheet

Specifications



Rack PDU, Switched, 1U, 16A, 208/230V, (8)C13



AP7921

! Discontinued on: 30 June 2021

! To be end-of-service on: 28 June 2023

! To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V 230 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Cable length	2.50 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets User manual

Physical

Colour	Black
Height	4.4 cm
Width	44.5 cm
Depth	10.8 cm
Net weight	2.27 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

[In] rated current	16 A
Permissible voltage	200...240 V
Input current limits	20 A
Load capacity	3680 VA

Network frequency	50/60 Hz
-------------------	----------

Output

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

Conformance

Product certifications	cUL listed CE CSA GOST IRAM MIC UL listed VDE VCCI
------------------------	--

Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
-----------	--

Environmental

Ambient air temperature for operation	0...45 °C
---------------------------------------	-----------

Relative humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-25...65 °C
-------------------------------------	-------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0.00...15240.00 m
------------------	-------------------

Packing Units

Package 1 Weight	3.45 kg
------------------	---------

Package 1 Height	7 cm
------------------	------

Package 1 width	48.6 cm
-----------------	---------

Package 1 Length	34.3 cm
------------------	---------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Lead free	Yes
-----------	-----

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	---------------------

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Take-back	Take-back program available
-----------	-----------------------------

Contractual warranty

Warranty

2 years repair or replace

Recommended replacement(s)

AP7921 is replaced by:

1x



Rack PDU, Switched, 1U, 16A, 208/230V, (8)C13

AP7921B
