

# Product data sheet

Specifications



## Rack PDU, Switched, 1U, 15A, 100/120V, (8)5-15

AP7900

⚠ Discontinued on: Nov 10, 2023

⚠ Discontinued

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Color	Black
Pdu Type	Switched
Cord Length	12 ft (3.66 m)
Number Of Cables	1
Provided Equipment	Cord retention bracket(s) Horizontal mounting brackets User Manual Installation guide

### Complementary

Input Voltage	100 V 120 V
Height	1.73 in (4.4 cm)
Width	17.52 in (44.5 cm)
Output Voltage	120 V
Depth	4.25 in (10.8 cm)
Net Weight	5.00 lb(US) (2.27 kg)
Mounting Location	Front
Mounting Preference	No preference
Input Plug Type	NEMA 5-15P
Mounting Mode	Rack-mounted
Rack Units	1U
Mounting Position	Horizontal
Line Rated Current	12 A
Acceptable Input Voltage	100...120 V
Input Current Limits	15 A
Load Capacity	1440 VA
Input Frequency	50/60 Hz
Outlet Type And Quantity	8 NEMA 5-15R

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Product Certifications	cUL Listed UL Listed
Standards	FCC Part 15 class A ICES-003
Ambient Air Temperature For Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage Altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

Gtin	731304205722
------	--------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	13.50 in (34.3 cm)
Package 1 Length	18.50 in (47 cm)
Package 1 Weight	7.61 lb(US) (3.45 kg)

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



Energy Efficient   Take-back   Transparency

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Lead Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

Eu Rohs Directive   Compliant with Exemptions

Environmental Disclosure   [Product Environmental Profile](#)

Circularity Profile   [End of Life Information](#)