

# Product datasheet

Specifications



## Line-R 1200VA Automatic Voltage Regulator

LE1200I

 To be discontinued on: 30 Apr 2024

 To be discontinued

### Overview

Lead Time Usually in Stock

### Main

Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	230 V
Rated Power In W	1200 W
Rated Power In Va	1200 VA
Input Connection Type	IEC 60320 C14
Provided Equipment	User manual

### Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

### Physical

Colour	Beige
Height	11.6 cm
Width	21.4 cm
Depth	14.1 cm
Net Weight	4.2 kg
Mounting Preference	Lower
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

### Input

Network Frequency	47...63 Hz
Input Voltage Limits	160...290 V

### Output

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Configurable Power In W	1200 W
---------------------------------	--------

## Conformance

Product Certifications	C-Tick CE GOST
Standards	EN 55024 EN 60950

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

## Surge Protection and Filtering

Surge Energy Rate	300 J
-------------------	-------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	27.3 cm
Package 1 Length	20.7 cm
Package 1 Weight	4.5 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	44 cm
Package 2 Width	23 cm
Package 2 Length	43 cm
Package 2 Weight	19.76 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	108
Package 3 Height	145.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	533.52 kg
Scc14	10731304197932

## Contractual warranty


Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

## Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins