Product data sheet

Specifications



Rack PDU, Switched, ZeroU, 12.5kW, 208V, (21) C13&(3) C19;3' Cord

AP7968B

Overview

Lead Time Usually in Stock

Main

mam	
Color	Black
Pdu Type	Switched
Cord Length	3 ft (0.91 m)
Number Of Cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets RS-232 configuration cable Toolless Mounting Kit

Complementary

Input Voltage	208 V 3 phase
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Output Voltage	208 V
Depth	3.50 in (8.9 cm)
Net Weight	17.81 lb(US) (8.08 kg)
Mounting Location	Side
Mounting Preference	No preference
Mounting Mode	Rack-mounted
Rack Units	0U
Mounting Position	Vertical
Max Line Current	35 A
Input Current Limits	35 A
Load Capacity	12500 VA
Input Frequency	50/60 Hz
Number Of Input Connectors	1 CS8365
Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19

Environment



Product Certifications	cUL Listed CSA Industry Canada UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950
Ambient Air Temperature For Operation	23113 °F (-545 °C)
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	595 %
Storage Altitude	050000 ft (0.0015240.00 m)

Ordering and shipping details

Gtin 731304331650

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	82.99 in (210.8 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	24.34 lb(US) (11.04 kg)

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

R	esc	our	ce	pei	rfor	m	an	ce
• •		-	UU	PO.		••••	~ · · ·	~

\checkmark	Energy Efficient Product	
⊘	Take-Back Program Available	

Well-being performance			
②	Lead Free		
②	Mercury Free		
⊘	Rohs Exemption Information	Yes	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information