

Product data sheet

Specifications



APC Premium Audio/Video Surge Protector 8 Outlet with Coax Protection, 120V

P8V

! Discontinued on: 01 December 2021

! End-of-service on: 05 March 2022

! Discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	6 ft (1.83 m)
Number of cables	1
Provided equipment	6ft Gold-plated coaxial cable 6ft High speed internet cable

Physical

Color	Black
Height	15.51 in (39.4 cm)
Width	3.74 in (9.5 cm)
Depth	2.01 in (5.1 cm)
Net Weight	2.09 lb(US) (0.95 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Maximum Line Current per phase	15 A

Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

Conformance

Product Certifications	CSA
------------------------	-----

Equipment protection policy	Lifetime : \$100000
UL 1449 TVSS Rating	330

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...50000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Data Line Protection	Cable modem/video protection
Let Through Voltage Rating	330 V
Data Lines Protected(multi-line only)	1
NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	70 dB
Peak current	40 kA common mode 20 kA normal mode
Surge energy rating	4720 J

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304260141
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.72 in (45 cm)
Package 1 Width	7.09 in (18 cm)
Package 1 Length	2.36 in (6 cm)
Package 1 Weight	2.71 lb(US) (1.227 kg)
SCC14	10731304260148

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration


Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	Lifetime
----------	----------


Recommended replacement(s)

P8V is replaced by the following product range:



SurgeArrest Home/Office
Professional-grade Electrical Surge Protection for Computers and Electronics
Products: 15

Or P8V is replaced by:

1x 

APC Home Office SurgeArrest 8 Outlet with Phone (Splitter) and Coax Protection, 120V
P8VT3