

# Product datasheet

Specifications



## APC 19" Rack LCD Console

AP5719

### Overview

<b>Presentation</b>	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
<b>Lead time</b>	Usually in Stock

### Main

<b>Main Input Voltage</b>	100 V 240 V
<b>Number of rack unit</b>	1U
<b>Provided equipment</b>	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Rack mounting hardware Single user rack mount kit USB cable USB KVM cable

### Physical

<b>Colour</b>	Black
<b>Height</b>	4.4 cm
<b>Width</b>	48.2 cm
<b>Depth</b>	66.5 cm
<b>Net weight</b>	17.4 kg
<b>Mounting location</b>	Front Rear
<b>Mounting preference</b>	No preference
<b>Mounting mode</b>	Rack-mounted
<b>Maximum mounting depth</b>	104.98 cm
<b>Minimum mounting depth</b>	68 cm

### Input

<b>Network frequency</b>	50/60 Hz
--------------------------	----------

### Conformance

<b>Product certifications</b>	C-Tick CE
-------------------------------	--------------

Industry Canada  
KCC  
NOM  
UL listed  
VCCI class A  
VDE  
TAA compliance

---

<b>Standards</b>	EN 55022 class A EN 55024 EN 60950 FCC part 15 class A IEC 60950
------------------	--

---

## Environmental

---

<b>Ambient air temperature for operation</b>	0...40 °C
--	-----------

---

## Supported Hardware

---

<b>Display size</b>	19 inch
<b>Trackball type</b>	PS/2 touchpad USB mouse
<b>Display type</b>	LCD display
<b>Display power consumption</b>	19 W
<b>Pixel size</b>	0.26

---

## Packing Units

---

<b>Package 1 Weight</b>	20.99 kg
<b>Package 1 Height</b>	15.2 cm
<b>Package 1 width</b>	67.3 cm
<b>Package 1 Length</b>	82.6 cm

---

## Offer Sustainability

---

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Lead free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Take-back</b>	Take-back program available

---

## Contractual warranty

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

---