## **Product datasheet**

Specifications





# power cord kit (6 ea) - locking - C19 to C20 (90 degree) - 0.6m

AP8712R

#### Overview

Presentation

Fresentation	equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead Time	Usually in Stock
Main	
Input Connection Type	IEC 60320 C20
Cable Length	0.61 m
Number Of Cables	6
Provided Equipment	3 left-angle jumper cords 3 right-angle jumper cords
Physical	
Colour	Black
Height	30 cm
Width	6 cm
Depth	6 cm
Net Weight	1.12 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Input	
Max Line Current	16 A

#### Conformance

Power Cable Length

**Number Of Power Socket Outlets** 

16 A

0.61 m

1 IEC 60320 C19

Output

Max Current Draw

Product Certifications	ccc	
	CSA	
	PSE	
	UL listed	
	VDE	

## **Environmental**

Ambient Air Temperature For Operation	075 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.0015240.00 m

## **Packing Units**

r adming dimes	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	6 cm
Package 1 Length	6 cm
Package 1 Weight	1.12 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	13
Package 2 Height	26 cm
Package 2 Width	33.8 cm
Package 2 Length	56.5 cm
Package 2 Weight	15 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	13
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	15 kg
Scc14	10731304279676

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

## Resource performance



Take-Back Program Available

### Well-being performance



Lead Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information