

# Product datasheet

Specifications



## rack PDU - basic - 0U - 10A 230V - (15)C13



AP9568

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Colour	Black
Pdu Type	Basic
Cord Length	1.98 m
Number Of Cables	1
Provided Equipment	Installation guide Rack mounting brackets Toolless mounting kit

### Complementary

Input Voltage	120 V 200 V 208 V 230 V 240 V
Height	61 cm
Width	4.4 cm
Output Voltage	208 V 230 V
Depth	4.4 cm
Net Weight	2 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	0U
Mounting Position	Vertical
Permissible Voltage	100...240 V
Input Current Limits	10 A
Load Capacity	2300 VA
Network Frequency	50/60 Hz
Total Number Of Outlets	15 IEC 60320 C13

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Product Certifications	cUL listed CE GOST Queensland Australia UL listed VDE
Ambient Air Temperature For Operation	0...45 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	64.8 cm
Package 1 Width	17.8 cm
Package 1 Length	15.2 cm
Package 1 Weight	2.724 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability




**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)




Energy Efficient   Take-back   Transparency   RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>