



SECTION 1: IDENTIFICATION

Product identifier:

Product name:	Rechargeable Li-ion Mobile Power
Other names:	Not available.
Model Numbers:	MXXYY-ZZ where (XX is the battery size in WH and is less than 20, YY is the color, and ZZ is the location, North America if no ZZ).
Country:	USA / CANADA
Product type:	Solid

Identified uses

Not available

Manufacturer

Supplier/Manufacturer:	Schneider Electric IT USA (formerly APC by Schneider Electric, APC Sales and Service Corp.)
Address:	132 Fairgrounds Road West Kingston, RI 02892
Telephone:	800-788-2208 or 401-789-5735
E-mail:	http://nam-en.apc.com/app/ask
Website:	www.APC.com
Telecopy:	Not available.

Emergency telephone number (with hours of operation)

CANUTEC: +1-613-996-6666 or *666 (cellular)

SECTION 2: HAZARDS IDENTIFICATION

OSHA/HCS status:

While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this SDS contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and available for employees and other users of this product.

Classification of the substance or mixture:

Not classified.

GHS label elements:

Signal word: No signal word.
Hazard statements: No known significant effects or critical hazards.

Precautionary statements

Prevention:	Not applicable
Response	Not applicable
Storage	Not applicable
Disposal	Not applicable

Hazards not otherwise classified (HNOC)

Physical hazards not otherwise classified (PHNOC): None known.
Health hazards not otherwise classified (HHNOC): None known.

SECTION 3: COMPOSITION / INFORMATION ON INGREDIENTS

Substance/Mixture: Mixture.
Other means of identification: Not available.

CAS number/other identifiers

CAS number: Not applicable.
Product code: Not available.

USA: This battery pack is an article pursuant to 29 CFR 1910.1200 and, as such, is not subject to the OSHA Hazard Communication Standard requirement. The information contained in this Safety Data Sheet contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and available for employees and other users of this product.

Canada: This is not a controlled product under WHMIS. This product meets the definition of a “manufactured article” and is not subject to the regulations of the Hazardous Products Act.

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section. Occupational exposure limits, if available, are listed in Section 8.

SECTION 4: FIRST AID MEASURES

Description of necessary first aid measures

Eye contact	Contact with the contents of an opened cell can cause burns. Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
Inhalation	If contents of an opened cell are inhaled, remove source of contamination or move victim to fresh air. Get medical attention if symptoms occur.
Skin contact	Contact with the contents of an opened cell can cause burns. Flush contaminated skin with plenty of water. Get medical attention if symptoms occur.
Ingestion	Contact with the contents of an opened cell can cause burns. Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

Most important symptoms/effects, acute and delayed

Potential acute health effects

Eye contact	No known significant effects or critical hazards.
Inhalation	No known significant effects or critical hazards.
Skin contact	No known significant effects or critical hazards.
Ingestion	No known significant effects or critical hazards.

Over-exposure signs/symptoms

Eye contact	No known significant effects or critical hazards.
Inhalation	No known significant effects or critical hazards.
Skin contact	No known significant effects or critical hazards.
Ingestion	No known significant effects or critical hazards.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician	Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled
Specific treatments	No specific treatment
Protection of first-aiders	No action shall be taken involving any personal risk or without suitable training

See toxicological information (Section 11).

SECTION 5 : FIRE-FIGHTING MEASURES

Extinguishing media

Suitable extinguishing media	Use an extinguishing agent suitable for the surrounding fire.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Lithium ion batteries contain flammable liquid electrolyte that may vent, ignite and produce sparks when subjected to high temperatures (> 150 °C (302 °F)), when damaged or abused (e.g., mechanical damage or electrical overcharge). Burning cells can ignite other batteries in close proximity.
Hazards thermal decomposition products	Decomposition products may include the following materials: <ul style="list-style-type: none">- Carbon dioxide- Carbon monoxide- Halogenerated compounds- Metal oxide/oxides
Special protective actions for fire-fighters	No special measures are required.
Special protective equipment for fire-fighters	Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	No action shall be taken involving any personal risk or without suitable training. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Put on appropriate personal protective equipment.
For emergency responders	If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For nonemergency personnel".
Environmental precautions	Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

SECTION 7: HANDLING AND STORAGE

Precautions for safe handling

Protective measures	Put on appropriate personal protective equipment (see Section 8).
Advice on general occupational hygiene	Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.
Conditions for safe storage, including any incompatibilities	Store in accordance with local regulations. Store battery pack in a dry location. Keep at room temperature (25°C +/-5°C). Elevated temperatures can result in shortened cell life.

SECTION 8: EXPOSURE CONTROLS / PERSONAL PROTECTION

Control parameters

United States Occupational exposure limits

None

Canada

Occupational exposure limits		TWA (8 hours)			STEL (15 mins)			Ceiling			Notations
Ingredient	List name	ppm	mg/m ³	Other	ppm	mg/m ³	Other	ppm	mg/m ³	Other	
Aluminium	US ACGIH 3/2015	-	1	-	-	-	-	-	-	-	[a]
	AB 4/2009	-	10	-	-	-	-	-	-	-	[3][b]
	BC 2/2015	-	1	-	-	-	-	-	-	-	[c]
	ON 7/2015	-	1	-	-	-	-	-	-	-	[a]
	QC 1/2014	-	10	-	-	-	-	-	-	-	
Copper	US ACGIH 3/2015	-	1	-	-	-	-	-	-	-	[d]
	US ACGIH 3/2015	-	0.2	-	-	-	-	-	-	-	[e]
	AB 4/2009	-	1	-	-	-	-	-	-	-	[d]
		-	0.2	-	-	-	-	-	-	-	[e]
	BC 2/2015	-	1	-	-	-	-	-	-	-	[d]
		-	0.2	-	-	-	-	-	-	-	[e]
	ON 7/2015	-	1	-	-	-	-	-	-	-	[d]
		-	0.2	-	-	-	-	-	-	-	[e]
	QC 1/2014	-	1	-	-	-	-	-	-	-	[d]
		-	0.2	-	-	-	-	-	-	-	[e]
Graphite, synthetic	US ACGIH 3/2015	-	2	-	-	-	-	-	-	-	[a]
	AB 4/2009	-	2	-	-	-	-	-	-	-	[f]
	BC 2/2015	-	2	-	-	-	-	-	-	-	[c]
	ON 7/2015	-	2	-	-	-	-	-	-	-	[a]
	QC 1/2014	-	2	-	-	-	-	-	-	-	[g]

[3] Skin sensitization

Form: [a]Respirable fraction [b]Metal Dust [c]Respirable [d]Dusts and mists [e]Fume [f]Respirable (all forms except graphite fibres) [g]Respirable dust.

Appropriate engineering controls	Good general ventilation should be sufficient to control worker exposure to airborne contaminants.
Environmental exposure controls	Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.

Individual protection measures

Hygiene measures	Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
Eye/face protection	Not required under normal conditions of use. Wear safety glasses if handling an open or leaking cell.
Hand protection	Not required under normal conditions of use. Wear neoprene or natural rubber gloves if handling an open or leaking cell.
Body protection	Not required under normal conditions of use.
Other skin protection	Not required under normal conditions of use.
Respiratory protection	Not required under normal conditions of use.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical state	Solid. [Cell. Prismatic.]
Color	Multicolor.
Odor	Odorless.
Odor threshold	Not applicable.
pH	Not applicable.
Melting point	Not applicable.
Boiling point	Not applicable.
Flash point	Not applicable.
Evaporation rate	Not applicable.
Flammability (solid, gas)	Not applicable.
Lower and upper explosive (flammable) limits	Not applicable.
Vapor pressure	Not applicable.
Vapor density	Not applicable.
Relative density	Not applicable.
Solubility in water	Insoluble in the following materials: cold water and hot water.
Partition coefficient: n-octanol/water	Not applicable.
Auto-ignition temperature	Not applicable.
Decomposition temperature	Not applicable.
Viscosity	Not applicable.

SECTION 10: STABILITY AND REACTIVITY

Reactivity	No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	The product is stable.
Possibility of hazardous reactions	Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	No specific data.
Incompatible materials	Reactive or incompatible with the following materials: oxidizing materials, acids and alkalis.
Hazardous decomposition products	Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: TOXICOLOGICAL INFORMATION

Information on toxicological effects

Acute toxicity	There is no data available.														
Irritation/Corrosion	There is no data available.														
Sensitization	There is no data available.														
Mutagenicity	There is no data available.														
Carcinogenicity	Classification														
	<table border="1"> <thead> <tr> <th>Product name</th> <th>OSHA</th> <th>IAR C</th> <th>NTP</th> <th>ACGIH</th> <th>EPA</th> <th>NIOSH</th> </tr> </thead> <tbody> <tr> <td>Aluminium</td> <td>-</td> <td>-</td> <td>-</td> <td>A4</td> <td>-</td> <td>-</td> </tr> </tbody> </table>	Product name	OSHA	IAR C	NTP	ACGIH	EPA	NIOSH	Aluminium	-	-	-	A4	-	-
	Product name	OSHA	IAR C	NTP	ACGIH	EPA	NIOSH								
Aluminium	-	-	-	A4	-	-									
Reproductive toxicity	There is no data available.														
Teratogenicity	There is no data available.														
Specific target organ toxicity (single exposure)	There is no data available.														
Specific target organ toxicity (repeated exposure)	There is no data available.														
Aspiration hazard	There is no data available.														

Information on the likely routes of exposure: Dermal contact, Eye contact, Inhalation, Ingestion.

Potential acute health effects

Eye contact	No known significant effects or critical hazards.
Inhalation	No known significant effects or critical hazards.
Skin contact	No known significant effects or critical hazards.
Ingestion	No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact	No known significant effects or critical hazards.
Inhalation	No known significant effects or critical hazards.
Skin contact	No known significant effects or critical hazards.
Ingestion	No known significant effects or critical hazards.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects	No known significant effects or critical hazards.
Potential delayed effects	No known significant effects or critical hazards.

Long term exposure

Potential immediate effects	No known significant effects or critical hazards.
Potential delayed effects	No known significant effects or critical hazards.

Potential chronic health effects

General	No known significant effects or critical hazards.
Carcinogenicity	No known significant effects or critical hazards.
Mutagenicity	No known significant effects or critical hazards.
Teratogenicity	No known significant effects or critical hazards.
Developmental effects	No known significant effects or critical hazards.
Fertility effects	No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates: There is no data available.

SECTION 12: ECOLOGICAL INFORMATION

Toxicity	There is no data available.
Persistence and degradability	There is no data available.
Bioaccumulative potential	There is no data available.

Mobility in soil






Soil/water partition coefficient (K_{oc})	No data available.
Other adverse effects	No known significant effects or critical hazards.

SECTION 13: DISPOSAL CONSIDERATIONS

Disposal methods

The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: TRANSPORT INFORMATION

	DOT	TDG	IMDG	IATA
UN number	UN3481	UN3481	UN3481	UN3481
UN proper shipping name	LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT (including lithium ion polymer batteries). Marine pollutant	LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT (including lithium ion polymer batteries)	LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT (including lithium ion polymer batteries)	LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT (including lithium ion polymer batteries)
Transport hazard class(es)	9  	9 	9 	9 
Packing group	II	II	II	II
Environmental hazards	Yes.	No.	No.	No.

Additional information	This product is not regulated as a marine pollutant when transported on inland waterways in sizes of ≤5 L or ≤5 kg or by road, rail, or inland air in non-bulk sizes, provided the packagings meet the general provisions of §§ 173.24 and 173.24a.	Product classified as per the following sections of the Transportation of Dangerous Goods Regulations: 2.43-2.45 (Class 9).	-	The environmentally hazardous substance mark may appear if required by other transportation regulations.
-------------------------------	---	---	---	--

AERG : 147

Special precautions for user	Transport within user's premises: always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not available.

SECTION 15: REGULATORY INFORMATION

U.S. Federal regulations	TSCA 8(a) CDR Exempt/Partial exemption: Not determined. United States inventory (TSCA 8b): All components are listed or exempted. Clean Water Act (CWA) 307: Copper.
Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)	Listed.
Clean Air Act Section 602 Class I Substances	Not listed.
Clean Air Act Section 602 Class II Substances	Not listed.
DEA List I Chemicals (Precursor Chemicals)	Not listed.
DEA List II Chemicals (Precursor Chemicals)	Not listed.

SARA 302/304

Composition/information on ingredients
No products were found
SARA 304 RQ: Not applicable

SARA 311/312

Classification: Not applicable.
Composition/information on ingredients.
No products were found.

SARA 311/312

No products were found.

SARA 313

	Product name	CAS number	%
Form R –Reporting requirements	Aluminium	7429-90-5	≥5 - <10
	Copper	7440-50-8	≥5 - <10
Supplier notification	Aluminium	7429-90-5	≥5 - <10
	Copper	7440-50-8	≥5 - <10

SARA 313 notifications must not be detached from the SDS and any copying and redistribution of the SDS shall include copying and redistribution of the notice attached to copies of the SDS subsequently redistributed.

State regulations

Massachusetts	The following components are listed: Graphite, synthetic; Aluminium; Copper
New York	The following components are listed: Copper
New Jersey	The following components are listed: Graphite, synthetic; Aluminium; Copper
Pennsylvania	The following components are listed: Graphite, synthetic; Aluminium; Copper

California Prop. 65

No products were found.

Canada - Canadian lists

Canadian NPRI	The following components are listed: Aluminium; Copper.
CEPA Toxic substances	None of the components are listed.
Canada inventory	All components are listed or exempted.

SECTION 16: OTHER INFORMATION

Review date: October, 13th, 2015

Version: 1

Key to abbreviations:

- ATE = Acute Toxicity Estimate
- BCF = Bioconcentration Factor
- GHS = Globally Harmonized System of Classification and Labelling of Chemicals
- IATA = International Air Transport Association
- IBC = Intermediate Bulk Container
- IMDG = International Maritime Dangerous Goods
- LogPow = logarithm of the octanol/water partition coefficient
- MARPOL 73/78 = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
- UN = United Nations

Notice to reader:

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.