

## Basic Rack PDU


## Overview

The American Power Conversion (APC®) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

**Outlets.** The Rack PDU has twenty IEC-320-C13 outlets, and four IEC-320-C19 outlets.

**Power cord.** The 10-foot (3.05-meter) power cord terminates with a NEMA L6-30 connector.

## **AP7541**



## **Specifications**

NEMA L6-30 plug
20 – IEC-320-C13, 4 – IEC 320-C19 outlets
200 – 240 VAC
± 10% of normal voltage
50/60 Hz
30 A (24 A (UL(C-UL) derated)
(2) 20-A, 2-pole circuit breakers
63.75 × 2.19 × 1.73 in (161.92 × 5.56 × 4.39 cm)
84.00 × 6.00 × 5.00 in (213.36 × 15.24 × 12.7 cm)
12.25 lb (5.56 kg)
14.25 lb (6.46 kg)
0-10,000 ft (0-3000 m) 0-50,000 ft (0-15 000 m)
-5 to 45° C (23 to 115° F) -25 to 65° C (-13 to 149° F)
5-95% RH non-condensing 5-95% RH non-condensing
UL (C-UL) listed, PSE

Customer support and warranty information is available at the APC Web site, www.apc.com.

 $\ \, \mathbb O$  2009 APC by Schneider Electric. All trademarks are owned by Schneider Electric Industries S.A.S., American Power Conversion Corporation, or their affiliated companies.

