



# Certainty in a connected world

## APC Back-UPS™ 650

Power and protect your critical electronics from damage due to power outages, surges and spikes while providing short term battery power during an outage. The Back-UPS 650 protects your equipment and network connection in harsh power environments, ensuring maximum productivity while maintaining work efficiency.

[www.apc.com](http://www.apc.com)

# APC Back-UPS™



Power and protect your critical electronics from damage due to power outages, surges and spikes while providing short term battery power during an outage. The Back-UPS 650 protects your equipment and network connection in harsh power environments, ensuring maximum productivity while maintaining work efficiency.

## Certainty in a connected world

The new APC Back-UPS 650 combines high value features with affordable pricing.

1

### 4 IEC “Battery Backup & Surge Protected” Sockets

Power and protect your critical electronics equipment that require battery back-up along with surge protection allowing you to save your work and protect your data when the power goes out or fluctuates at dangerous levels.

2

### Push Button Circuit Breaker

Easily recover from circuit overloads and protect your fuse box and electronics from electrical damage.


3

### LED Indicator and Audible Alarms

Quickly understand your UPS unit and power status through visual and audible indicators.

### 2 Year Warranty

APC assures customer peace of mind offering a 2 year warranty with free technical phone and online support.



### APC Back-UPS 650 Applications

- PC and Peripherals
- Networking equipment (router, modem)
- Network Attached Storage (NAS)
- Game console
- Projector with impulse power
- Landline cordless phone

# APC Back-UPS

## BC650I-RSX Technical Specifications

<b>Output</b>	
Output Capacity	650VA / 360 Watts
Output Voltage / Frequency (On utility)	230V / 50/60 +/- 3Hz
Output Voltage / Frequency (On battery)	230V +/- 8% 50 or 60 Hz +/- 1Hz (auto-sensing)
Output Connections	4 IEC sockets All with battery backup and surge protection
Waveform Type	Stepped Approximation to Sine Wave
<b>Input</b>	
Maximum Adjustable Input Voltage	160 – 278 V
Input Over Current Protection	7A Circuit Breaker
Input Power Cord	Removable input power cord with Schuko plug
<b>Surge Protection</b>	
AC Power Surge Protection	All Sockets
<b>Physical</b>	
Unit Dimensions (H x W x D)	200 x 115 x 256 mm
Unit Weight	5.5 Kg
Shipping Dimensions (H x W x D)	343.5 x 200 x 278.5 mm
Shipping Weight	6.2 Kg
Color	Black
UPC Code	731304331759
<b>Battery</b>	
Battery Type	Maintenance-free, sealed lead-acid battery, leak proof
Typical Recharge Time	8 hrs
<b>Management</b>	
Alarms	Visual (LED) and audible alarms
Adjustable Sensitivity and Transfer Voltage	Low, Medium (default), High
<b>In the box</b>	
IEC 320 C13- C14 output power cord * 2	