

Product datasheet

Specifications



APC Smart-UPS SRT 3000VA 230V

SRT3000XLI

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	2700 W
Rated power in VA	3000 VA
Input Connection Type	BS1363A British IEC 60320 C20 Schuko CEE 7 / EU1-16P
Nb of power socket outlets	8 IEC 60320 C13 2 IEC Jumpers 2 IEC 60320 C19
Cable length	2.44 m
Number of cables	3
Battery type	Lead-acid battery
Provided equipment	CD with software Country-specific detachable power cord Documentation CD Installation guide Removable support feet USB cable Warranty card

General

Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	8.5 cm
Depth	63.5 cm
Net weight	31.3 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Vertical

Input

Network frequency	40...70 Hz auto-sensing
Input voltage limits	100...275 V adjustable (half load)

Output

Maximum configurable power in W	2700 W
Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Bypass type	Internal bypass (automatic and manual)
Maximum configurable power in VA	3000 VA

Conformance

Product certifications	CE EAC RCM VDE
Marking	CE Mark
Standards	EN/IEC 62040-1 EN/IEC 62040-2

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0.00...15240.00 m

Acoustic level	55 dBA
Heat dissipation	703 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Battery recharge time	3 h
Number of battery replacement quantity	1
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery voltage	96 V
Battery charger power	168 W rated
Battery power in VAH	505 VAh runtime
Battery life	3...5 year(s)
Battery option	SRT96BP 1 1515 VAh SRT96BP 2 2525 VAh SRT96BP 3 3535 VAh SRT96BP 4 4545 VAh SRT96BP 5 5555 VAh SRT96BP 6 6565 VAh SRT96BP 8 8585 VAh SRT96BP 10 10605 VAh
Extended runtime	1

Communications & Management

Free slots	1
Control panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms prioritized by severity
Emergency power off	Yes

Surge Protection and Filtering

Surge energy rate	340 J
-------------------	-------

Packing Units

Package 1 Weight	36.74 kg
Package 1 Height	24.6 cm
Package 1 width	59.9 cm
Package 1 Length	87.1 cm
Number of Units in Package 3	6

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
-----------------	---
