

Product datasheet

Specifications



Power Cord Kit (6 EA), Locking, C19 TO C20, 0.6M (2FT), Red

AP8712SX340

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Input Connection Type	IEC 60320 C20
Cable Length	0.61 m
Number Of Cables	6

Physical

Colour	Red
Height	30 cm
Width	6 cm
Depth	6.5 cm
Net Weight	1.12 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Max Line Current	16 A
Input Current Limits	16 A

Output

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Power Cable Length	0.61 m

Conformance

Product Certifications	CCC CSA PSE UL listed VDE
------------------------	---------------------------------------

Environmental

Ambient Air Temperature For Operation	0...75 °C
Relative Humidity	20...80 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	6.5 cm
Package 1 Length	6 cm
Package 1 Weight	1.12 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information