


Product datasheet

Specifications



MGE Galaxy 3500 Extended Run Frame, with MCCB, with 2 Battery Modules Exp. to 6

G35TBXR2B6

! Discontinued

! Discontinued on: 5 July 2021

! End-of-service on: 18 Oct 2023

Overview

Lead Time Usually Ships within 2 Weeks

Main

Main Input Voltage 208 V 3 phases
400 V 3 phases

Battery Type Lead-acid battery

Provided Equipment Installation guide

Batteries & Runtime

Number Of Battery Blocks Per String 4

Number Of Battery Free Slots 4

Number Of Battery Filled Slots 2

Device Mounting Enclosed battery cabinet

Physical

Colour Grey

Height 149.9 cm

Width 52.3 cm

Depth 92.5 cm

Net Weight 388 kg

Mounting Mode Not rack-mountable

Input

Network Frequency 50/60 Hz

Conformance

Product Certifications CSA

Standards CSA C22.2 No 107.1

Environmental

Ambient Air Temperature For Operation 0...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Altitude	0...10000 ft
Relative Humidity	0...85 %
Ambient Air Temperature For Storage	0...30 °C
Storage Altitude	0.00...4572.00 m
Storage Relative Humidity	0...85 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	164.3 cm
Package 1 Width	106.2 cm
Package 1 Length	65 cm
Package 1 Weight	418 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
