

Product datasheet

Specifications



APC Smart-UPS RT 1000VA 230V - Marine



SURT1000XLIM

Overview

Presentation	High availability, ruggedized power protection for shipboard and other transportation applications.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	700 W
Rated power in VA	1000 VA
Input Connection Type	IEC 60320 C14
Output connection type	6 IEC 60320 2 IEC Jumpers
Number of rack unit	2U
Cable length	2.50 m
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	CD with software Relay board Smart UPS signalling RS-232 cable User manual

General

Number of power module	700
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
Variant option	Shipboard

Physical

Colour	Black
Height	43.2 cm
Width	8.5 cm
Depth	48.3 cm
Net weight	23 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	No

Input

Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Input voltage limits	180...280 V
Input Power Factor at Full Load	1

Output

Maximum configurable power in W	700 W
Harmonic distortion	Less than 3 %
Output frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Bypass type	Built-in bypass
Efficiency	88 % (full load)
Maximum configurable power in VA	1000 VA

Conformance


Product certifications	CE DNV KCC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...55 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing

Storage altitude	0.00...15240.00 m
Acoustic level	55 dBA
Heat dissipation	324 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Number of battery filled slots	1
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery charger power	109 W rated
Battery power in VAH	328 VAh runtime
Battery life	3...5 year(s)
Replacement battery	RBC31 
Battery option	SURT48XLBP 1 984 VAh SURT48XLBP 2 1640 VAh SURT48XLBP 3 2296 VAh SURT48XLBP 4 2952 VAh SURT48XLBP 5 3608 VAh SURT48XLBP 8 5576 VAh SURT48XLBP 10 6888 VAh
Extended runtime	1

Communications & Management

Free slots	0
Preinstalled device	Dry contact I/O smartslot card
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency power off	Optional

Surge Protection and Filtering

Surge energy rate	420 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28.6 cm
Package 1 Width	63 cm
Package 1 Length	59.4 cm
Package 1 Weight	27.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
-----------------	--

Recommended replacement(s)