Product datasheet

Specifications



Rack PDU, Metered, 1U, 12A/208V, 10A/230V, (8) C13



AP7820B

Overview

Lead Time Usually in Stock

Main

Pdu Type	Metered
Cord Length	1.98 m
Provided Equipment	Cord retention bracket(s) Installation guide Rack mounting brackets

Complementary

Input Voltage	200 V
	208 V
	230 V
Height	4.4 cm
Width	44.4 cm
Output Voltage	208 V
	230 V
Depth	10.2 cm
Net Weight	1.73 kg
Mounting Location	Front
	Rear
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	1U
Mounting Position	Horizontal
[In] Rated Current	10 A
Input Current Limits	15 A
Load Capacity	2300 VA
Rated Current	10 A - 230 V
	12 A - 208 V
Network Frequency	50/60 Hz
Total Number Of Outlets	8 IEC 60320 C13

Environment



Product Certifications	cUL listed C-Tick CE CSA GOST UL listed VDE VCCI
Standards	FCC part 15 class A UL 60950
Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	33.7 cm
Package 1 Length	47 cm
Package 1 Weight	2.91 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

R	esc	our	ce	pei	rfor	m	an	ce
• •		-	UU	PO.		••••	~ · · ·	~

\checkmark	Energy Efficient Product	
⊘	Take-Back Program Available	

Well-being performance			
②	Lead Free		
②	Mercury Free		
⊘	Rohs Exemption Information	Yes	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information