Product data sheet

Specification





APC NetShelter SX, Server Rack Enclosure, 42U, Black, 1991.4H x 750W x 1070D mm

AR3150

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	42U
Provided Equipment	Baying hardware Key(s)
	Keyed-alike doors and side panels Leveling feet
	Mounting hardware
	Pre-installed casters
	Side panels

Physical

Height	78.39 in (199.1 cm)
Width	29.53 in (75 cm)
Depth	42.13 in (107 cm)
Net Weight	343.83 lb(US) (155.96 kg)
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
Minimum Mounting Depth	10.31 in (26.19 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	2250 lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

Conformance

Standards UL 2416
UL 60950-1
EIA-310E

Packing Units



Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	83.35 in (211.7 cm)
Package 1 Width	33.50 in (85.1 cm)
Package 1 Length	45.51 in (115.6 cm)
Package 1 Weight	370.77 lb(US) (168.18 kg)

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile