

Product datasheet

Specifications



Rack PDU 2G, Switched, ZeroU, 16A, 230V, (7) C13 & (1) C19, IEC309 Cord

AP8958EU3

Overview

Presentation	APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
Lead Time	Usually in Stock

Main

Colour	Black
Pdu Type	Switched
Cord Length	3.00 m
Number Of Cables	1
Provided Equipment	Installation guide Locking input power cord Rack mounting brackets Serial configuration cable Safety guide

Complementary

Input Voltage	200 V 208 V 230 V
Height	98.8 cm
Width	5.6 cm
Output Voltage	200 V 208 V 230 V
Depth	4.6 cm
Net Weight	3.23 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 16 A 2P + E
Mounting Mode	Not rack-mountable

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rack Units	0U
Mounting Position	Vertical
[In] Rated Current	16 A
Permissible Voltage	220...240 V
Max Line Current	16 A
Input Current Limits	16 A
Load Capacity	3700 VA
Network Frequency	50/60 Hz
Total Number Of Outlets	7 IEC 60320 C13 1 IEC 60320 C19

Environment

Product Certifications	cUL listed PSE UL listed VCCI class A VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC part 15 class A ICES-003
Ambient Air Temperature For Operation	-5...60 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	112.5 cm
Package 1 Width	16.5 cm
Package 1 Length	11.4 cm
Package 1 Weight	5.488 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)




Energy Efficient Take-back


Resource performance


 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins