

# Product datasheet

Specifications



## Galaxy VS Maintenance Bypass Panel, single unit, 150kW 400V wallmount

GVSBPUS150KH

### Overview

|                     |   |
|---------------------|---|
| <b>Presentation</b> | Maintenance bypass cabinet for complete isolation of the UPS during service operations. |
| <b>Lead time</b>    | Usually Ships within 2 Weeks  |

### Main

|                           |                |
|---------------------------|----------------|
| <b>Main Input Voltage</b> | 400 V 3 phases |
|---------------------------|----------------|

### Physical

|                   |       |
|-------------------|-------|
| <b>Height</b>     | 80 cm |
| <b>Width</b>      | 60 cm |
| <b>Depth</b>      | 28 cm |
| <b>Net weight</b> | 48 kg |

### Environmental

|  |                         |
|--|-------------------------|
| <b>Ambient air temperature for operation</b> | 0...40 °C               |
| <b>Operating altitude</b>                    | 0...3000 ft             |
| <b>Relative humidity</b>                     | 0...95 % non-condensing |
| <b>Ambient air temperature for storage</b>   | -25...55 °C             |
| <b>Storage Relative Humidity</b>             | Non-condensing 0...95 % |

### Packing Units

|                         |       |
|-------------------------|-------|
| <b>Package 1 Weight</b> | 48 kg |
| <b>Package 1 Height</b> | 80 cm |
| <b>Package 1 width</b>  | 60 cm |
| <b>Package 1 Length</b> | 28 cm |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| <b>EU RoHS Directive</b> | Under investigation   |
| <b>WEEE</b>              | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |