

# Product datasheet

Specifications

## APC SERVICE BYPASS PDU, 230V 10AMP W/ (6) IEC C13



SBP1500RMI

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Main Input Voltage	230 V
Product Or Component Type	Bypass kit
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C14
Number Of Rack Unit	2U
Cable Length	1.98 m
Number Of Cables	1
Provided Equipment	User manual Rack mounting brackets

### Physical

Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	7.6 cm
Net Weight	2 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted

### Input

Network Frequency	50/60 Hz
Permissible Voltage	220...240 V
Max Line Current	10 A
Input Current Limits	10 A
Load Capacity	1500 VA
Power Factor	0...1

### Output

Max Current Draw	10 A
------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Power Socket Outlets	6 IEC 60320 C13 1 IEC Jumpers
Number Of Power Socket Outlets	6
Protection Type	Circuit breaker
Power Cable Length	1.22 m
Efficiency	99 %

## Conformance

Product Certifications	VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...15000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.1 cm
Package 1 Width	46.3 cm
Package 1 Length	29.5 cm
Package 1 Weight	3.5 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	56
Package 2 Height	113 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	195.608 kg

## Contractual warranty



Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins