

# Product datasheet

Specifications



## APC Back-UPS Pro, 1500VA/865W, Tower, 230V, 6x 6A Indian outlets, AVR, LCD, User Replaceable Battery

BR1500G-IN

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	230 V
Rated power in W	865 W
Rated power in VA	1500 VA
Output connection type	4 India 3-pin 6A 2 India 3-pin 6A surge
Cable length	1.52 m
Number of cables	1
Battery type	Lead-acid battery

### General

Provided equipment	telephone cable user manual USB cable warranty card
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

### Physical

Colour	Black
Height	30.1 cm
Width	11.4 cm
Depth	38.2 cm
Net weight	11.76 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

## Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	India 3-pin 16A
Input voltage limits	170...294 V

## Output

Maximum configurable power in W	865 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains
UPS type	Line interactive
Wave type	Stepped approximation to a sinewave
Efficiency	85 % (full load) 86 % (half load)
Maximum configurable power in VA	1500 VA
Transfer time	6 ms typical : 10 ms maximum



## Conformance

Product certifications	BIS
------------------------	-----

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m
Acoustic level	45 dBA

## Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	7.2 h
Number of battery replacement quantity	1
Additional information	9Ah x 2 internal batteries
Battery charger power	30 W rated
Battery power in VAh	216 VAh runtime
Battery life	2...4 year(s)
Replacement battery	<a href="#">APCRBC124</a>  <a href="#">APCRBC144</a> 
Battery option	BR24BPG-IN 1 432 VAh
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several v

---

Extended runtime	0
------------------	---

## Communications & Management

---

Control panel	Multifunction LCD status and control console
---------------	--

---

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
-------	--

## Surge Protection and Filtering

---

Surge energy rate	680 J
-------------------	-------

---

Let through voltage rating	330 V
----------------------------	-------

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

---

Number of Units in Package 1	1
------------------------------	---

---

Package 1 Height	38.1 cm
------------------	---------

---

Package 1 Width	48.3 cm
-----------------	---------

---

Package 1 Length	22.9 cm
------------------	---------

---

Package 1 Weight	13.19 kg
------------------	----------

---

SCC14	10731304268793
-------	----------------

## Offer Sustainability

---

Sustainable offer status	Green Premium product
--------------------------	-----------------------

---

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

---

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
-------------------	--

---

Mercury free	Yes
--------------	-----

---

RoHS exemption information	<a href="#">Yes</a>
----------------------------	---------------------

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---

---

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

---

Take-back	Take-back program available
-----------	-----------------------------

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)