

Product datasheet

Specifications



APC Smart-UPS 1000VA, Tower, LCD 230V with SmartConnect Port

SMC1000IC

Overview

Presentation Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Other Input Voltage 220 V
240 V

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Rated power in W 600 W

Rated power in VA 1000 VA

Input Connection Type IEC 320 C14

Output connection type 8 IEC 60320 C13

Battery type Lead-acid battery

Provided equipment Power cord
USB cable

General

Number of power module filled slots 0

Number of power module free slots 0

Product web sub-family Cloud-enabled monitoring

Redundant No

Physical

Colour Black

Height 21.9 cm

Width 17.1 cm

Depth 43.9 cm

Net weight 17.27 kg

Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	170...300 V adjustable 180...287 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1000 VA
Maximum configurable power in W	600 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance


Product certifications	CE GOST VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	41 dBA
Heat dissipation	100 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1

Battery life	3...5 year(s)
Replacement battery	APCRBC142 
Battery power in VAH	216 VAh runtime
Battery charger power	72 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Free slots	0

Surge Protection and Filtering

Surge energy rate	455 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	37.6 cm
Package 1 Width	59.5 cm
Package 1 Length	32.8 cm
Package 1 Weight	19.55 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)