

Product datasheet

Specifications



APC Back-UPS 2000VA, 230V, without battery with selectable charger and flooded/SMF compatible

BX2000UXI

Overview

Lead time Usually in Stock

Main

Main Input Voltage	230 V
Rated power in W	1200 W
Rated power in VA	2000 VA
Output connector type	Hard wire 3-wire (H N + E) 1
Cable length	0.46 m

General

Provided equipment	user manual warranty card
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Height	22 cm
Width	14.5 cm
Depth	39.2 cm
Net weight	13.4 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Network frequency	40...70 Hz
-------------------	------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Maximum configurable power in W	1200 W
Output frequency	50 Hz +/- 1 Hz unsynchronised
UPS type	Line interactive
Waveform Type	Stepped approximation to a sinewave
Efficiency	92 % (full load) 90 % (half load)
Maximum configurable power in VA	2000 VA
Transfer time	8 ms typical : 12 ms maximum

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...3000 ft
Ambient air temperature for storage	0...45 °C
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0.00...914.40 m
Acoustic level	50 dBA

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery power in VAh	0 VAh runtime
Extended runtime	0

Communications & Management

Control panel	LED Status display with on line : on battery
---------------	--

Packing Units

Package 1 Weight	14.3 kg
Package 1 Height	33.5 cm
Package 1 width	23.5 cm
Package 1 Length	47.7 cm
Package 3 Height	12.6 cm
Package 3 width	100 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------
