
Product datasheet

Specifications








AP4430

! Discontinued on: 9 Jun 2023



Overview

Lead Time Usually in Stock

Main

Main	
Main Input Voltage	200 V 208 V
Main Output Voltage	200 V 208 V
Input Connection Type	NEMA L6-20P
Number Of Rack Unit	1U
Cable Length	2.44 m
Number Of Cables	2
Provided Equipment	Mounting hardware Rack mounting brackets RS-232 configuration cable

Physical

Height	4.4 cm
Width	43.2 cm
Depth	23.6 cm
Net Weight	4.83 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Input

Network Frequency	50/60 Hz
[In] Rated Current	16 A
Max Line Current	20 A
Input Current Limits	20 A
Load Capacity	3300 VA

Output

Max Current Draw 20 A

Number Of Power Socket Outlets	8 IEC 60320 C13 1 IEC 60320 C19
Protection Type	Without circuit breaker

Conformance

Standards	EN 55022 class A
	FCC part 15 class A

Environmental

Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	35.6 cm
Package 1 Length	60 cm
Package 1 Weight	6.6 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Lead Free



Mercury Free



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information