

# Product datasheet

Specifications



APC Smart-UPS, Line Interactive, 2200VA, Tower, 230V, 8x IEC C13+2x IEC C19 outlets, SmartConnect Port+SmartSlot, AVR, LCD

SMT2200IC

## Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

## Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	1980 W
Rated power in VA	2200 VA
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Output connection type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Number of rack unit	0U
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	USB cable

## General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Cloud-enabled monitoring
Redundant	No

## Physical

Colour	Black
--------	-------

Height	43.5 cm
Width	19.7 cm
Depth	54.4 cm
Net weight	50.2 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

## Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	2200 VA
Maximum configurable power in W	1980 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

## Conformance


Product certifications	CE EAC RCM VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

## Environmental

Acoustic level	45 dBA
Heat dissipation	275 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
------------------------	--

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)
Replacement battery	<a href="#">RBC55</a> 
Battery power in VAH	783 VAh runtime
Battery charger power	260 W rated

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1

## Surge Protection and Filtering

Surge energy rate	365 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	69.9 cm
Package 1 Width	76.2 cm
Package 1 Length	38.1 cm
Package 1 Weight	61.9 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

**Recommended replacement(s)**