Product datasheet

Specification





APC NetShelter Basic Rack PDU, 0U, 1PH, 3.3kW, 100-240V 20A or 200-240V 16A, 13 C13 outlets, C20 inlet

AP6020A

Overview

Presentation	Reliable rack power distribution designed to increase manageability and efficiency in the data center The output and input connections are (13) C13 Real-time remote monitoring of connected loads User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.
Lead Time	Usually in Stock
Main	
Colour	Black
Pdu Type	Basic
Provided Equipment	Installation guide Safety guide
Complementary	
Input Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Height	38.8 cm
Width	4.4 cm
Depth	9.3 cm
Net Weight	1.5 kg
Mounting Location	Front Rear
Mounting Preference	Lower
Input Plug Type	IEC 60320 C20
Mounting Mode	Not rack-mountable
Rack Units	1U
Usb Compatible	No
Mounting Position	Horizontal
[In] Rated Current	16 A
Permissible Voltage	100240 V
Max Line Current	20 A
Input Current Limits	20 A

3300 VA

Load Capacity

Network Frequency	50/60 Hz
Total Number Of Outlets	13 IEC 60320 C13

Environment

Product Certifications	cUL listed	
	CE	
	EAC	
	IRAM	
	PSE	
	UL listed	
	VDE	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.6 cm
Package 1 Width	7.6 cm
Package 1 Length	21 cm
Package 1 Weight	2.02 kg
Scc14	10731304327803

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

Lead Free

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant

EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information