

# Product datasheet

Specifications



## MGE Galaxy 5500 30KVA 400V Integrated Parallel UPS 15 Minutes, Start-up 5x8

G55TUPSM30HB15S

! Discontinued

! Discontinued on: 5 Jul 2021

! End-of-service on: 18 Oct 2023

### Overview

Presentation	A versatile 3-phase UPS for facility, industrial and data center applications. Configurable system with a comprehensive range of accessories to meet your application demands.
Lead Time	Usually Ships within 2 Weeks

### Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated Power In W	27000 W
Rated Power In Va	30000 VA
Output Connector Type	Hard wire 4-wire (3P + E) 1
Battery Type	VRLA
Provided Equipment	Installation guide Network management card Start-up service User manual

### Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	10 h
Additional Information	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Battery Voltage	432 V
Battery Charger Power	1449 W rated
Battery Power In Vah	14500 VAh runtime
Battery Life	8...10 year(s)
Battery Graph Comments	Estimated runtimes based on battery vendor data, at typical environmental conditions, with no electrical input and balanced PF = 0.9 output.
Extended Runtime	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## General

Bypass Voltage Tolerance	+/- 10 % settable from +/- 4/6/8 and 10 %
Max Bypass Input Current	43 A
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

## Physical

Height	190 cm
Width	71.2 cm
Depth	85.5 cm
Net Weight	958 kg
Mounting Preference	No preference
Usb Compatible	No

## Input

Network Frequency	45...65 Hz
Number Of Input Connectors	1 hard wire 4-wire (3P + E) 1 hard wire 4-wire (3P + N)
Input Voltage Limits	250...470 V adjustable 323...437 V 380 V 340...460 V 400 V 353...477 V 415 V
Maximum Input Current	46 A
Switching Current Capacity	125 A
Max Short Time Withstand Current	20 kA
Input Harmonic Distortion	Less than 3 % for full load
Input Protection Type	3-pole circuit breaker
Inrush Current	200 A peak
Load Power Factor	0.9
Input Power Factor At Full Load	1

## Output

Maximum Configurable Power In W	27000 W
Harmonic Distortion	Less than 2 %
Output Frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	3 : 1
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 5% at 100% load step
Output Harmonic Distortion	< 1% linear load and < 2.5% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Required Output Current Protection	43 A

Bypass Type	Built-in maintenance bypass Built-in static bypass Optional external bypass
Efficiency	92.4 % (full load)
Maximum Output Current	190 A
Maximum Configurable Power In Va	30000 VA

## Conformance

Product Certifications	CE TÜV VDE
Standards	IEC 62040-1-2 EN/IEC 62040-2 EN/IEC 62040-3 ISO 9001

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-20...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...12192.00 m
Acoustic Level	55.5 dBA
Ip Degree Of Protection	IP20

## Communications & Management

Free Slots	2
Preinstalled Device	Network management card 2 with environmental monitoring, out of band access and Modbus
Control Panel	Multifunction LCD status and control console
Emergency Power Off	Yes

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203 cm
Package 1 Width	96 cm
Package 1 Length	98 cm
Package 1 Weight	978 kg

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up, 1 year (parts only)
----------	--

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

Eu Rohs Directive	Under investigation
-------------------	---------------------

---