Product data sheet

Specifications





Power Cord, Locking C19 to C20, 3.0m

AP8760

Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead Time	Usually in Stock

Main

Input Connection Type	IEC 60320 C20
Cable Length	3.05 m
Number Of Cables	1

Physical

Colour	Black
Height	23 cm
Width	23 cm
Depth	4.5 cm
Net Weight	0.51 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Output

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Power Cable Length	3.05 m

Conformance

Product Certifications	CCC	
	CSA	
	PSE	
	UL listed	
	VDE	



Environmental

Ambient Air Temperature For Operation	075 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23 cm
Package 1 Width	23 cm
Package 1 Length	4.5 cm
Package 1 Weight	0.51 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information