

APC Smart-UPS SRT 72V 2.2kVA RM Battery Pack



SRT72RMBP

Overview

Lead Time Usually in Stock

Main

Number Of Rack Unit	2U
Battery Type	Lead-acid battery
Provided Equipment	Documentation CD Installation guide Rack mounting brackets

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Battery Voltage	72 V
Number Of Battery Replacement Quantity	2
Replacement Battery	APCRBC141 ☐

Physical

Colour	Black	
Height	8.5 cm	
Width	43.2 cm	
Depth	59.4 cm	
Net Weight	33.9 kg	
Mounting Mode	Rack-mounted	

Conformance

Standards OSHPD

Environmental

Ambient Air Temperature For Operation	040 °C
Operating Altitude	010000 ft
Relative Humidity	095 % non-condensing
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m

Storage Relative Humidity 0...95 % non-condensing

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.9 cm
Package 1 Width	59.9 cm
Package 1 Length	83.1 cm
Package 1 Weight	40.82 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	2
Package 2 Height	100 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	93.64 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information