

Product data sheet

Specifications



APC SERVICE BYPASS PDU, 230V 16AMP W/ (6) IEC C13 AND (1) C19

SBP3000RMI

Overview

Lead time Usually in Stock

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C20
Number of rack unit	2U
Cable length	2.50 m
Number of cables	1
Provided equipment	User manual Rack mounting brackets

Physical

Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	7.6 cm
Net weight	2.09 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Network frequency	50/60 Hz
Permissible voltage	220...240 V
Max line current	16 A
Input current limits	16 A
Load capacity	3000 VA
Power factor	0...1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Max current draw	16 A
Number of power socket outlets	6 IEC 60320 C13 1 IEC Jumpers 1 IEC 60320 C19
Number of power socket outlets	7
Protection type	Circuit breaker
Power cable length	1.00 m
Efficiency	99 %

Conformance

Product certifications	VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.1 cm
Package 1 Width	29.5 cm
Package 1 Length	46.3 cm
Package 1 Weight	3.91 kg
Number of Units in Package 3	56

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)