

Product datasheet

Specifications



APC Easy UPS BVX 1600VA, 230V, AVR, India Sockets

BVX1600LI-IN

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Input voltage	230 V
Output voltage	230 V
Output voltage	230 V
Rated power in W	900 W
Rated power in VA	1600 VA
Nb of power socket outlets	5 India 2/3-pin 6A
Cable length	1.22 m
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	User manual

General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

Physical

Colour	Black
Height	19.0 cm
Width	14.0 cm
Depth	39.0 cm
Net weight	10.2 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0

USB compatible	No
----------------	----

Input

Network frequency	40...70 Hz +/- 5 Hz auto-sensing
Plug standard	India 3-pin 16A
Input voltage limits	140...300 V
Input protection type	Circuit breaker

Output

Maximum configurable power in W	900 W
Output frequency	50/60 Hz +/- 1 Hz unsynchronised
UPS type	Line interactive
Wave type	Stepped approximation to a sine wave
Graph display	1
Maximum configurable power in VA	1600 VA
Transfer time	6 ms typical : 10 ms maximum

Conformance

Product certifications	BIS
------------------------	-----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0...15000 m
Acoustic level	40 dBA
IP degree of protection	IP20

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	6 h
Battery voltage	24 V
Battery capacity	7 Ah
Extended runtime	0

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rate	255 J
-------------------	-------

Packing Units

Package 1 Weight	11.2 kg
------------------	---------

Package 1 Height	29.7 cm
------------------	---------

Package 1 width	23.5 cm
-----------------	---------

Package 1 Length	49.5 cm
------------------	---------

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	-----

China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
-----------------------	---

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Contractual warranty

Warranty	2 Years on UPS & 1 Year on Battery
----------	------------------------------------
