

# Product datasheet

Specifications



APC Easy UPS On-Line, 3kVA,  
Rackmount 2U, 230V, 3x India + 1x  
Hard wire 3-wire(1P+N+E) outlets,  
Intelligent Card Slot, No battery, W/  
O rail kit

SRV3KUXI-IN

## Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead Time	Usually in Stock

## Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	2400 W
Rated Power In Va	3000 VA
Output Connection Type	3 India 3-pin 6A
Output Connector Type	Hard wire 3-wire (1P + N + E) 1
Number Of Rack Unit	2U
Provided Equipment	1 USB cable 1 RS-232 configuration cable 1 rack mounting brackets 1 stabilization/wall mounting feet 1 battery cable user manual

## Batteries & Runtime

Efficiency	<a href="#">View Efficiency Graph</a>
Battery Type	External battery system
Battery Voltage	72 V
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Charger Power	700 W rated

## General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Physical

Colour	Black (RAL 7010)
Height	8.6 cm
Width	43.8 cm
Depth	46.2 cm
Net Weight	10.1 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit
Usb Compatible	Yes
Mounting Position	Horizontal

## Input

Input Voltage Limits	110...280 V half load 160...280 V full load
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E)
Input Protection Type	Circuit breaker
Network Frequency	40...70 Hz auto sensing

## Output

Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2400 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Harmonic Distortion	3 %
Ups Type	Double conversion online
Wave Type	Sine wave
Efficiency	90 % (full load)
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass Type	Internal bypass (automatic and manual)
Crest Factor	3 : 1

## Conformance

Product Certifications	BIS
------------------------	-----

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m
Ambient Air Temperature For Storage	-20...60 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m
Acoustic Level	50 dBA

Heat Dissipation	910 Btu/h
Ip Degree Of Protection	IP20

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off	Yes
Control Panel	Multifunction LCD status and control console

## Surge Protection and Filtering

Surge Energy Rate	600 J
-------------------	-------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	70 cm
Package 1 Length	54.5 cm
Package 1 Weight	13.7 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

### Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	