



APC Smart-UPS, Line Interactive, 750VA, Rackmount 2U, 230V, 4x IEC C13 outlets, Network Card, AVR, LCD

SMT750RMI2UNC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices. Usually in Stock				
Lead Time					
Main					
Main Input Voltage	230 V				
Other Input Voltage	220 V 240 V				
Main Output Voltage	230 V				
Other Output Voltage	220 V 240 V				
Rated Power In W	500 W				
Rated Power In Va	750 VA				
Input Connection Type	IEC 320 C14				
Output Connection Type 4 IEC 320 C13 2 IEC Jumpers					
Number Of Rack Unit	2U				
Battery Type	Lead-acid battery				
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting support rails Smart UPS signalling RS-232 cable Temperature probe USB cable				

Batteries & Runtime

Run Time	View Runtime Graph ☐					
Extended Runtime	0					
Number Of Battery Filled Slots	0					
Number Of Battery Free Slots	0					
Battery Recharge Time	3 h					
Number Of Battery Replacement Quantity	1					
Battery Life	35 year(s)					
Replacement Battery	APCRBC123 ☐					
Battery Charger Power	56 W rated					

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Physical

•	
Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	40.6 cm
Net Weight	17.24 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	1
Usb Compatible	Yes

Input

Input Voltage Limits	151302 V adjustable 160286 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic Distortion	Less than 5 %
Maximum Configurable Power In Va	750 VA
Maximum Configurable Power In W	500 W
Transfer Time	2 ms typical
Ups Type	Line interactive
Wave Type	Sine wave
Output Frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE EAC RCM VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level	42 dBA
Heat Dissipation	46 Btu/h
Operating Altitude	010000 ft

Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

Control Panel Multifunction LCD status and control console						
Emergency Power Off	Optional					
Preinstalled Device Network management card 3 with environmental monitoring						
Control Panel	LED status display with on line : on battery : replace battery and overload indicators					
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays					

Surge Protection and Filtering

Surge Energy Rate 459 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.1 cm
Package 1 Width	58.4 cm
Package 1 Length	54.6 cm
Package 1 Weight	21.18 kg

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

R	esc	our	ce	pei	rfor	m	an	ce
• •		-	\mathbf{c}	PC.		••••		v

V	nergy Επισιέπτ Product
⊘	ake-Back Program Available

Well-being performance				
⊘	Lead Free			
⊘	Mercury Free			
②	Rohs Exemption Information	Yes		

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information