

Power Cord, C13 to C14, 2.5m



AP9870

Overview

Lead Time Usually in Stock

Main

Input Connection Type	IEC 60320 C14
Cable Length	2.50 m
Number Of Cables	1

Physical

Colour	Black
Height	3.8 cm
Width	7.6 cm
Depth	20.3 cm
Net Weight	0.23 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	50/60 Hz
Permissible Voltage	90250 V
Max Line Current	10 A
Input Current Limits	10 A

Output

Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Protection Type	Without circuit breaker

Conformance

Product Certifications	CSA	
	UL listed	
	VDF	

Environmental

Ambient Air Temperature For	045 °C
Operation	

Relative Humidity	095 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	095 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	10.2 cm
Package 1 Length	20.3 cm
Package 1 Weight	0.3 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	25
Package 2 Height	25 cm
Package 2 Width	35 cm
Package 2 Length	56 cm
Package 2 Weight	9.1 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	25
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	9.1 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Lead Free

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant

EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

End of Life Information