


Product data sheet

Specifications



APC Easy UPS On-Line, 3kVA,
Lithium-ion, Rack/Tower 4U, 230V,
6 IEC C13 + 1 IEC C19 outlets,
Intelligent Card Slot, Extended
runtime, W/ rail kit

SRVL3KRILRK

Overview

Presentation	Double-conversion On-line UPS with Lithium-Ion battery to scalable runtime. Ideal UPS for essential power protection needs even in the most unstable power conditions.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	230 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	2700 W
Rated Power In Va	3000 VA
Input Connection Type	IEC 60320 C20
Output Connection Type	6 IEC 60320 C13 1 IEC 60320 C19
Number Of Rack Unit	4U
Provided Equipment	Basic UPS signalling RS-232 cable USB cable RJ45 cable RJ11 cable C13-C14 power cord IEC-C20 - Shuko input power cord Rack mounting brackets Stabilization feet User manual Safety guide Battery cable

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Li-Ion (Lithium-Ion)
Battery Voltage	48 V
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	4.8 h

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery Design Life	8...10 year(s)
Battery Life	8...10 year(s)
Battery Charger Power	500 W

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Physical

Colour	Black with silver front bezel
Height	17.2 cm
Width	43.8 cm
Depth	61.6 cm
Net Weight	38.3 kg
Usb Compatible	Yes
Mounting Position	Horizontal and vertical

Input

Input Voltage Limits	160...300 V full load 110...300 V 60 % load
Network Frequency	40...70 Hz auto-sensing

Output

Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2700 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Ups Type	Double conversion online
Wave Type	Sine wave
Efficiency	90 % (full load)
Bypass Type	Internal bypass (automatic and manual)
Crest Factor	3 : 1

Conformance

Product Certifications	CB CE RCM EAC TISI UKCA KC UN 38.3 IEC 62619
------------------------	--

Environmental

Ambient Air Temperature For Operation	0...40 °C
---------------------------------------	-----------

Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m
Acoustic Level	50 dBA
Heat Dissipation	1024 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off	Yes
Control Panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge Energy Rate	945 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	48 cm
Package 1 Width	80 cm
Package 1 Length	60 cm
Package 1 Weight	50.62 kg

Contractual warranty

Warranty	3 years UPS repair or replace; 5 years battery repair or replace
----------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins