



Ref. Certif. No.

**DK-63692-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

**CB TEST CERTIFICATE**

Product

Uninterruptible Power Supplies

Name and address of the applicant

Schneider Electric IT Corporation, FKA APC American Power Conversion  
132 Fairgrounds Road, PO Box 278, West Kingston, Rhode Island, 02892, USA

Name and address of the manufacturer

Schneider Electric IT Corporation, FKA APC American Power Conversion  
132 Fairgrounds Road PO Box 278 West Kingston, Rhode Island, 02892, USA

Name and address of the factory

Note: When more than one factory, please report on page 2

Schneider Electric Information Technology (Xiamen) Co Ltd  
1678 JIXIAN RD TONGJI PARK TORCH HI-TECH INDUSTRIAL  
XIAMEN FUJIAN 361100  
CHINA

Additional Information on page 2

Ratings and principal characteristics

See Page 2 and 3

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

Galaxy VX, GVXP250KD

Additional information (if necessary may also be reported on page 2)

National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62040-1(ed.1), IEC 62040-1(ed.1);am1

As shown in the Test Report Ref. No. which forms part of this Certificate

4787852903 issued on 2017-05-24

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2017-05-24

Signature:

Jan-Erik Storgaard

## Factories:

Schneider Electric IT Corporation, FKA APC American Power Conversion  
1660 Scenic Ave Costa Mesa CA 92626-1410  
USA

Schneider Electric IT USA, Inc., FKA APC American Power Conversion  
14875 Monte Vista Ave Chino CA 91710-5736  
USA

Schneider Electric IT USA, Inc., FKA APC American Power Conversion  
201 FULLING MILL RD MIDDLETOWN PA 17057-2921  
USA

Schneider Electric IT Corporation, FKA APC American Power Conversion  
132 Fairgrounds Rd PO BOX 278 West Kingston RI 02892  
USA

AMERICAN POWER CONVERSION (APC) BV, FKA APC AMERICAN POWER CONVERSION  
2ND ST CAVITE EPZAROSARIO 4106 CAVITE  
PHILIPPINES

AMERICAN POWER CONVERSION (APC) BV, FKA APC AMERICAN POWER CONVERSION  
PLANT 3 BLK 16, PHASE IV, LOT 10 PEZA ROSARIO 4106 CAVITE  
PHILIPPINES

Schneider Electric IT Business India Private Limited, FKA APC American Power Conversion  
NO 71 DODDATHOGURE VILLAGE ELECTRONIC CITY BEGUR HOBLI BANGALORE KA 561229  
INDIA

APC INDIA PVT LTD  
NO 18A SUVEY NO 128 1ST PHASE JIGANI INDUSTRIAL AREA JIGANI VILL. JIGANI HOBLI ANEKALTALUK  
BANGALORE KA 562106  
INDIA

## Ratings:

## Galaxy VX:

Configurations 500 kW/kVA, 500 kW/kVA N+1:

Input: 380/400/415 V, 886/851/819 A, 50/60 Hz or 480 V, 728 A, 50/60 Hz.

Bypass: 380/400/415 V, 767/729/703 A, 50/60 Hz or 480 V, 606 A, 50/60 Hz.

Output: 380/400/415 V, 760/722/696 A, 50/60 Hz or 480 V, 601 A, 50/60 Hz, Power factor 1, 500 kW/kVA

Configurations 625kW/kVA. 625 kW/kVA N+1:

Input: 380/400/415 V, 1107/1063/1024 A, 50/60 Hz or 480 V, 910 A, 50/60 Hz.

Bypass: 380/400/415 V, 959/911/878 A, 50/60 Hz or 480 V, 757 A, 50/60 Hz.

Output: 380/400/415 V, 950/902/870 A, 50/60 Hz or 480 V, 752 A, 50/60 Hz, Power factor 1, 625 kW/kVA

Configurations 500 kW/kVA expandable to 750 kW/kVA, 750 kW/kVA, 750 kW/kVA N+1:

Input: 380/400/415 V, 1328/1276/1229 A, 50/60 Hz or 480 V, 1092 A, 50/60 Hz.

Bypass: 380/400/415 V, 1151/1093/1054 A, 50/60 Hz or 480 V, 909 A, 50/60 Hz.

Output: 380/400/415 V, 1140/1083/1043 A, 50/60 Hz or 480 V, 902 A, 50/60 Hz, Power factor 1

Configuration 500 kW/kVA expandable to 750 kW/kVA: 500 kW/kVA

Configurations 750 kW/kVA, 750 kW/kVA N+1: 750 kW/kVA

## Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/nbcnames](http://www.ul.com/nbcnames)

Date: 2017-05-24

Signature:

Jan-Erik Storgaard

Configurations 500 kW/kVA expandable to 1000 kW/kVA, 625 kW/kVA expandable to 1000 kW/kVA, 750 kW/kVA expandable to 1000 kW/kVA, 1000 kW/kVA, 1000 kW/kVA N+1:  
Input: 380/400/415 V, 1771/1702/1638 A, 50/60 Hz or 480 V 1456 A, 50/60 Hz.  
Bypass: 380/400/415 V, 1535/1458/1405 A, 50/60 Hz or 480 V 1211 A, 50/60 Hz.  
Output: 380/400/415 V, 1519/1443/1391 A, 50/60 Hz or 480 V, 1203 A, 50/60 Hz, Power factor 1,  
Configuration 500 kW/kVA expandable to 1000 kW/kVA: 500 kW/kVA  
Configuration 625 kW/kVA expandable to 1000 kW/kVA: 625 kW/kVA  
Configuration 750 kW/kVA expandable to 1000 kW/kVA: 750 kW/kVA  
Configuration 1000 kW/kVA): 1000 kW/kVA  
Configuration 1000 kW/kVA N+1: 1000 kW/kVA

Configurations 1000 kW/kVA expandable to 1250 kVA, 1250 kW/kVA and 1250 kW/kVA N+1:  
Input: 380/400/415 V, 2214/2127/2048 A, 50 Hz or 480 V, 1820 A, 60 Hz.  
Bypass: 380/400/415 V, 1918/1822/1757 A, 50 Hz or 480 V, 1514 A, 60 Hz  
Output: 380/400/415 V, 1899/1804/1739 A, 50 Hz or 480 V, 1504 A, 60 Hz, Power factor 1  
Configuration 1000 kW/kVA expandable to 1250 kVA: 1000 kW/kVA  
Configurations 1250 kW/kVA and 1250 kW/kVA N+1: 1250 kW/kVA.

Configurations 1000 kW/kVA expandable to 1500 kVA, 1250 kW/kVA expandable to 1500 kVA, 1500 kW/kVA and 1500 kW/kVA N+1:  
Input: 380/400/415 V, 2657/2552/2457 A, 50 Hz or 480 V, 2184 A, 60 Hz  
Bypass: 380/400/415 V, 2302/2187/2108 A, 50 Hz or 480 V, 1817 A, 60 Hz  
Output: 380/400/415 V, 2279/2165/2087 A, 50 Hz or 480 V, 1804 A, 60 Hz, Power factor 1  
Configuration 1000 kW/kVA expandable to 1500 kVA: 1000 kW/kVA  
Configuration 1250 kW/kVA expandable to 1500 kVA: 1250 kW/kVA  
Configurations 1500 kW/kVA and 1500 kW/kVA N+1: 1500 kW/kVA.

GVXP250KD  
380/400/415 or 480 V  
50/60 Hz  
Input current: 380/400/415 V, 448/426/410 A or  
480 V, 364 A, 50/60 Hz  
Output current: 380/400/415 V, 380/360/348 A or  
480 V, 300 A, 50/60 Hz  
Power factor 1, 250 kW/kVA

#### Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/nbnames](http://www.ul.com/nbnames)

Date: 2017-05-24

Signature:

Jan-Erik Storgaard