Product data sheet

Specifications





Power Cord Kit (6 ea), Locking, C13 to C14, 0.6m

AP8702S-WW

Overview

Presentation	This Series of Rack Power Distribution Units (PDU) comes with Locking IEC Receptacles. The output and input connections are C13 to C14. The cord length is 0.6m. Locking IEC system allows the use of optional locking IEC power cords for added power cord security and enhanced reliability. No tools are required to disengage the locking feature and remove the plug from the locking receptacle.	
Lead Time	Usually in Stock	
Main		
Input Connection Type	IEC 60320 C14	
Cable Length	0.61 m	
Number Of Cables	6	
Physical		
Colour	Black	
Height	24 cm	
Width	7 cm	
Depth	4 cm	
Net Weight	0.7 kg	

Mounting Preference Mounting Mode

-

Input	
Max Line Current	10 A
Input Current Limits	10 A

No preference

Not rack-mountable

Output

Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Power Cable Length	0.61 m

Conformance

Product Certifications	CCC		
	PSE		
	VDE		

Environmental



Ambient Air Temperature For Operation	070 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	4 cm
Package 1 Length	7 cm
Package 1 Weight	0.7 kg

Contractual warranty

Warranty

2 years repair or replace

Sustainability

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.





Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Well-being performance

Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	



