

Product data sheet

Specifications



Power Cord, C13 to C14, 2.5m

AP9870



Overview

Lead time Usually in Stock

Main

Input Connection Type IEC 60320 C14

Cable length 2.50 m

Number of cables 1

Physical

Colour Black

Height 3.8 cm

Width 7.6 cm

Depth 20.3 cm

Net weight 0.23 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Network frequency 50/60 Hz

Permissible voltage 90...250 V

Max line current 10 A

Input current limits 10 A

Output

Max current draw 10 A

Number of power socket outlets 1 IEC 60320 C13

Protection type Without circuit breaker

Conformance

Product certifications CSA
UL listed
VDE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	10.2 cm
Package 1 Length	20.3 cm
Package 1 Weight	0.3 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	25 cm
Package 2 Width	35 cm
Package 2 Length	56 cm
Package 2 Weight	9.1 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	25
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	9.1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)