

# Product data sheet

Specifications



## APC Service Bypass Panel, 230V, 125A, 2x hardwire input connectors, 8x IEC 60320 C19 outlets

SBP20KRM14U

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Main Input Voltage	220 V 230 V 240 V 380 V 3 phases 400 V 3 phases 415 V 3 phases
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Number Of Rack Unit	4U
Number Of Cables	1
Provided Equipment	Installation guide Rack mounting brackets User manual

### Physical

Colour	Black
Height	17.8 cm
Width	43.2 cm
Depth	57.2 cm
Net Weight	18.78 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted

### Input

Network Frequency	50/60 Hz
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5 wire (3P + N + E)
Max Line Current	125 A
Input Current Limits	125 A
Load Capacity	20000 VA
Power Factor	0...1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Output

Max Current Draw	125 A
Number Of Power Socket Outlets	8 IEC 60320 C19
Protection Type	Circuit breaker
Efficiency	99 %

## Conformance

Product Certifications	CSA GOST
------------------------	-------------

## Environmental

Ambient Air Temperature For Operation	-20...50 °C
Relative Humidity	0...95 %
Operating Altitude	0...15000 ft
Ambient Air Temperature For Storage	-40...65 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	84.3 cm
Package 1 Length	61 cm
Package 1 Weight	31.36 kg

## Contractual warranty

Warranty	2 years (parts only)
----------	----------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins